



### Thorsman cable reels

#### Description

- Wide range of cable reels applicable with various applications for indoor and outdoor uses
- The range designed along innovative ergonomic lines with versatile features that offer superior comfort and smart functionality such as LED indicator, ergonomic handles for easy carrying and winding, safety thermal cut-out and fixed drum (for part of the models).

#### Application

- Thorsman cable reels could be used in any place, at any moment by any one. It's a reliable solution for all your at-home or on site needs
- Schneider Electric cable reels are the perfect choice for professional and DIY users.

### + Benefits

- Ergonomic design for easy carrying and winding
- Fixed drum to prevent the tangling of wires
- Led indicator to quickly and easily indicate and inform the user if the power is switched on
- Plug holder to prevent the cable from unwinding or snagging by keeping the plug fixed to the reel
- High performance cable HO7 RNF
- NF EN 61242

### Thorsman cable reels



Model/Type	Cable specification	Cable length (m)	IP	IK	Socket/Plug type	Ref. No.
Compact	HO5 VVF 3G1.0	15	20	-	Schuko	IMT33135
	HO5 VVF 3G1.5	15	20	-	Schuko	IMT33137
	HO5 VVF 3G1.5	15	44	-	Schuko	IMT33136
	HO5 VVF 3G1.0	15	20	-	DK	IMT33138
	HO5VVF 3G1.5	15	20	-	Contour	IMT33139
Classic	HO5 VVF 3G1.5	20	20	-	Schuko	IMT33140
	HO5VVF 2x1.0	25	20	-	DK	IMT33141
	HO5VVF 3G1.5	20	20	-	Contour	IMT33142
	HO5 VVF 3G1.25	25	20	-	BS 230V	IMT33143
	HO5 VVF 3G1.5	25	44	-	BS 110V	IMT33144
	HO5VVF3G1,5	25	44	-	Contour	IMT33145
	HO5 VVF 3G1.5	25	20	-	BS 230 V-RCD	IMT33146
Extended	HO5 VVF 3G1.5	25	44	-	Schuko	IMT33151
	HO5 VVF 2G1.0	40	20	-	DK	IMT33152
	HO7 RNF 3G2,5	25	44	-	Contour	IMT33153
	HO5 VVF 3G1.5	25	44	-	Contour	IMT33154
Advanced	HO5 VVF 2G1.0	40	20	08	DK	IMT33160
	HO5 VVF 3G1.5	40	44	08	Contour	IMT33156
	HO5 VVF 3G1.25	50	20	08	BS 230 V	IMT33157
	HO7 RNF 3G2,5	25	44	08	Contour	IMT33150
Professional	HO7 RNF 3G1.5	25	44	08	Schuko	IMT33147
	HO7 RNF 3G2.5	25	44	08	Schuko	IMT33148
	HO7 RNF 3G1.5	25	44	08	DK	IMT33149
	HO7 RNF 3G1.5	40	44	08	Schuko	IMT33158
	HO7 RNF 3G1.5	40	44	08	Contour	IMT33161
	HO7 RNF 3G1.5	40	44	08	DK	IMT33155