

Zs Figures for Mcbs

Circuit Breaker Max Zs Ohms @ 230V				Circuit Breaker Max Zs Ohms@230V				Circuit Breaker Max Zs Ohms@230V			
Type	Trip	0.4 Sec	5 Sec	Type	Trip	0.4 Sec	5 Sec	Type	Trip	0.4 Sec	5 Sec
C60H Type B	1A	46	46	C120H Type B	10A	4.6	4.6	NG125N/H Type B	80A	0.57	0.57
	2A	23	23		16A	2.88	2.88		100A	0.46	0.46
	4A	11.5	11.5		20A	2.3	2.3		125A	0.36	0.36
	6A	7.6	7.6		25A	1.84	1.84	Type C	10A	2.3	2.87
	10A	4.6	4.6		32A	1.44	1.44		16A	1.44	1.79
	16A	2.88	2.88		40A	1.15	1.15		20A	1.15	1.44
	20A	2.3	2.3		50A	0.92	0.92		25A	0.92	1.15
	25A	1.84	1.84		63A	0.73	0.73		32A	0.72	0.9
	32A	1.44	1.44		80A	0.57	0.57		40A	0.58	0.71
	40A	1.15	1.15		100A	0.46	0.46		50A	0.46	0.57
	50A	0.92	0.92		125A	0.36	0.36		63A	0.37	0.45
	63A	0.73	0.73	Type C	10A	2.3	2.87		80A	0.29	0.35
Type C	1A	23	29.49		16A	1.44	1.79	Type D	100A	0.23	0.28
	2A	11.5	14.38		20A	1.15	1.44		125A	0.18	0.23
	4A	5.75	7.42		25A	0.92	1.15		80A	0.21	0.35
	6A	3.88	4.89		32A	0.72	0.9		100A	0.16	0.28
	10A	2.3	2.95		40A	0.58	0.71		125A	0.13	0.23
	16A	1.44	1.84		50A	0.46	0.57				
	20A	1.15	1.47		63A	0.37	0.45				
	25A	0.92	1.18		80A	0.29	0.35				
	32A	0.72	0.92		100A	0.23	0.28				
	40A	0.58	0.74		125A	0.18	0.23				
	50A	0.46	0.59	Type D	10A	1.64	2.87				
	63A	0.37	0.47		16A	1.03	1.79				
Type D	1A	16.43	29.49		20A	0.82	1.44				
	2A	8.21	14.38		25A	0.66	1.15				
	4A	4.11	7.42		32A	0.51	0.9				
	6A	2.74	4.89		40A	0.41	0.71				
	10A	1.64	2.95		50A	0.33	0.57				
	16A	1.03	1.84		63A	0.26	0.45				
	20A	0.82	1.47		80A	0.21	0.35				
	25A	0.66	1.18		100A	0.16	0.28				
	32A	0.51	0.92		125A	0.13	0.23				
	40A	0.41	0.74								
	50A	0.33	0.59								
	63A	0.26	0.47								

Zs Figures for Mcbs

S