

Standard and Shallow Depth Light Modules

Table 19.273: Standard Light Modules for Types K, SK, and KX Control Units [121][122][123][124]


	Voltage	Description	Light Module	Voltage Assembly Code	Rating	Temperature Code T-Code	Replacement Lamp
			Type [125]				Part Number [121]
All		Full Voltage (without Bayonet Base Lamp)	KM40	40	—	—	None
6 Vac/Vdc		Full Voltage	KM31	31	.9 VA	T5	2550101020
6 Vac/Vdc		LED Red	KM31LR	31LR		T6	6508805201
6 Vac/Vdc		LED Green	KM31LG	31LG		T6	6508805203
6 Vac/Vdc		LED Yellow	KM31LY	31LY		T6	6508805202
12–14 Vac/Vdc		Full Voltage	KM32	32	1.2 VA	T5	2550101037
12–14 Vac/Vdc		LED Red	KM32LR	32LR		T6	6508805201
12–14 Vac/Vdc		LED Green	KM32LG	32LG		T6	6508805203
12–14 Vac/Vdc		LED Yellow	KM32LY	32LY		T6	6508805202
18 Vac/Vdc		Resistor	KM33	33	1.4 VA	T5	2550101037
24–28 Vac/Vdc		Full Voltage	KM35	35	1.2 VA	T3C	2550101002
24–28 Vac/Vdc		LED Red	KM35LR	35LR	.28 VA	T4	6508805210
24–28 Vac/Vdc		LED Green	KM35LG	35LG	.28 VA	T4	6508805212
24–28 Vac/Vdc		LED Yellow	KM35LY	35LY	.28 VA	T4	6508805211
24–28 Vac/Vdc		LED White	KM35LW	35LW	.28 VA	T4	6508805214
24–28 Vac/Vdc		LED Blue	KM35LL	35LL	.28 VA	T4	6508805213
48 Vac/Vdc		Full Voltage	KM36	36	2.6 VA	T3A	2550101025
110–120 V, 50–60 Hz		LED Red	KM1LR	1LR		T6	6508805201
110–120 V, 50–60 Hz		LED Green	KM1LG	1LG		T6	6508805203
110–120 V, 50–60 Hz		LED Yellow	KM1LY	1LY		T6	6508805202
110–120 V, 50–60 Hz		Transformer	KM1	1	2.4 VA	T6	2550101020
110–120 V, 50–60 Hz		Flashing	KMF1	F1	.85 VA	T6	2550101036
120 Vac/Vdc		Full Voltage/Resistor	KM38	38	3.0 VA	T4	2550101027
120 Vac/Vdc		Neon [126]	KM11	11	0.2 VA	T6	2550101013
120 Vac/Vdc		LED Red	KM38LR	38LR	1.4 VA	T4A	6508805210
120 Vac/Vdc		LED Green	KM38LG	38LG	1.4 VA	T4A	6508805212
120 Vac/Vdc		LED Yellow	KM38LY	38LY	1.4 VA	T4A	6508805211
120 Vac/Vdc		LED White	KM38LW	38LW	1.4 VA	T4A	6508805214
120 Vac/Vdc		LED Blue	KM38LL	38LL	1.4 VA	T4A	6508805213
208–220 V, 50–60 Hz		Transformer	KM3	3	2.5 VA	T6	2550101020
208–220 V, 50–60 Hz		LED Red	KM3LR	3LR		T6	6508805201
208–220 V, 50–60 Hz		LED Green	KM3LG	3LG		T6	6508805203
208–220 V, 50–60 Hz		LED Yellow	KM3LY	3LY		T6	6508805202
208–220 V, 50–60 Hz		LED White	KM3LW	3LW		T6	6508805215
208–220 V, 50–60 Hz		LED Blue	KM3LL	3LL		T6	6508805216
220–240 V, 50–60 Hz		Transformer	KM7	7	2.0 VA	T6	2550101020
220–240 V, 50–60 Hz		LED Red	KM7LR	7LR		T6	6508805201
220–240 V, 50–60 Hz		LED Green	KM7LG	7LG		T6	6508805203
220–240 V, 50–60 Hz		LED Yellow	KM7LY	7LY		T6	6508805202
220–240 V, 50–60 Hz		LED White	KM7LW	7LW		T6	6508805215
220–240 V, 50–60 Hz		LED Blue	KM7LL	7LL		T6	6508805216
240 Vac/Vdc		Resistor	KM25	25	6.0 VA	T3A	2550101027
240 Vac/Vdc		Neon [126]	KM12	12	0.3 VA	T6	2550101013
277 V, 50–60 Hz		Transformer	KM8	8	2.4 VA	T6	2550101020
380–480 V, 50–60 Hz		Transformer	KM5	5	2.8 VA	T6	2550101020
480 Vac/Vdc		Neon [126]	KM14	14	0.5 VA	T6	2550101013
550–600 V, 50–60 Hz		Transformer	KM6	6	2.5 VA	T6	2550101020


NOTE: Light modules are available in other voltages. For additional information, refer to Catalog 9001CT0001.

The products in Table 19.273 have been assigned Temperature Classifications (T-Codes) in accordance with UL 121201 (2017) — Nonincendive Electrical Equipment for Use in Class I and II, Division 2 and Class III, Divisions 1 and 2 Hazardous (Classified) Locations. These codes can aid the user in proper application of these products in accordance with ISO/ISA/IEC 60079-0 (2017-12) Explosive Atmospheres — Part 0: Equipment — General Requirements and the National Electric Code NFPA 70 — Article 500.

NOTE: Light modules shown in Table 19.274 are not UL Certified for use in hazardous locations.

Table 19.274: Shallow Depth Light Modules For Types K and SK Control Units [121] [123] [127] [122]

	Voltage	Description	Light Module	Voltage Assembly Code	Rating	Temperature Code T-Code	Replacement Lamp
			Type [125]				Part Number
	24–28 Vac/Vdc	Full Voltage	KM55	55	1.2 VA	—	2550101002
		LED Red	KM55LR	55LR	0.5 VA	—	6508805204
		LED Green	KM55LG	55LG		—	6508805206
		LED Yellow	KM55LY	55LY		—	6508805205
110–120 Vac/Vdc	Full Voltage	KM58	58	3.0 VA	—	2550101027	
	LED Red	KM58LR	58LR	0.5 VA	—	6508805204	
	LED Green	KM58LG	58LG		—	6508805206	
	LED Yellow	KM58LY	58LY		—	6508805205	



[121] For use with all operators except KX and remote test pilot.

[122] For use in hazardous locations—See Square D Offering According to Class, Division, and Group, page 19-92.

[123] With LED light modules, use either a clear color cap or a cap the same color as the LED.

[124] With neon type light modules, use a clear color cap only.

[125] When ordering, add prefix 9001 to the catalog number.

[126] Not for use on KX operators.

[127] Reduces the depth of illuminated push buttons with contact blocks by over 33%.