

Type of starter	ATS	01N1●●FT		01N206●● to 01N222●●			01N232●●			01N2●●LY, 01N2●●Q	
<p>Use</p> <p>Starting time</p> <p>Full voltage status or starter at standstill</p> <p>Operating cycle</p> <p>Starting time</p> <p>Maximum number of cycles per hour</p>	s	1	5	1	5	10	1	5	10	1	12
		100	20	100	20	10	50	10	5	360	30