

Type	Size	Motor rating (ND / HD)	Output current (ND / HD)	Dimensions		
				Width	Depth ⁽¹⁾	Height
ATV680C11Q4X1	1a	110 kW / 90 kW	210 A / 173 A	600 mm	600 mm	2150 mm
ATV680C13Q4X1		132 kW / 110 kW	250 A / 210 A	600 mm	600 mm	2150 mm
ATV680C16Q4X1		160 kW / 132 kW	302 A / 250 A	600 mm	600 mm	2150 mm
ATV680C20Q4X1	2a	200 kW / 160 kW	370 A / 302 A	1000 mm	600 mm	2150 mm
ATV680C25Q4X1		250 kW / 200 kW	477 A / 370 A	1000 mm	600 mm	2150 mm
ATV680C31Q4X1		315 kW / 250 kW	590 A / 477 A	1000 mm	600 mm	2150 mm
ATV680C35Q4X1	3a	355 kW / 280 kW	660 A / 520 A	1600 mm	600 mm	2150 mm
ATV680C40Q4X1		400 kW / 315 kW	730 A / 590 A	1600 mm	600 mm	2150 mm
ATV680C45Q4X1		450 kW / 355 kW	830 A / 650 A	1600 mm	600 mm	2150 mm
ATV680C50Q4X1		500 kW / 400 kW	900 A / 730 A	1600 mm	600 mm	2150 mm
ATV680C56Q4X1	4a	560 kW / 450 kW	1020 A / 830 A	2000 mm	600 mm	2150 mm
ATV680C63Q4X1		630 kW / 500 kW	1140 A / 900 A	2000 mm	600 mm	2150 mm
ATV680C71Q4X1	5a	710 kW / 560 kW	1260 A / 1020 A	2600 mm	600 mm	2150 mm
ATV680C80Q4X1		800 kW / 630 kW	1420 A / 1140 A	2600 mm	600 mm	2150 mm

(1) Total depth including door handle and switch handle: 664 mm