

| KEY | |
|-----|---|
| | Dimmable, with lamps on one dimmer up to a max of 10% of the max dimmer load (8 max tested) |
| | Lamps are dimmable for up to x number of lamps only |
| | Lamps are dimmable across full dimming range, but exhibit flickering at a single distinct position in the range (usually 80% light level point) |
| | The majority of configurations show undesirable dimming behavior |
| | Configuration not tested |
| | Lamp is not designed for use with this dimmer type |
| | Name New added since previous version |

| Brand | Type # | Type | Load | Bulbs | | | | Novature | | 230V Reflector | | | | MR16 | | |
|--------------------|---------------|-------|------------|--------|---------------|---------|-------|----------|----------|----------------|-------------------|-------|--------|-------|---------|----------|
| | | | | A55 6W | Glow Designer | 806lm | | Candle | Lustre | GU10 PF | GU10 7W & DimTone | PAR20 | PAR30S | PAR38 | MR16 7W | MR16 10W |
| Schneider | ALT400901 | RL | 600VA | | | | | | | | | | | | | |
| Schneider | MTN572599 | RL | 20-500W | | | | | | 2-21 | | | | | | | |
| Schneider | MTN572299 | R | 60-600W | | | | | | | | | | | | | |
| Schneider | STD400RC/RL | RLC | 40-400W | | | | | | | | | | | | | |
| Schneider | CCTDD200001 | RLC | 40-400W | | | | | | | | | | | | | |
| Schneider | CCTDD200002 | RLC | 40-400W | | | | | | | | | | | | | |
| Schneider | MTN577099 | R.L.C | 25-420W | | | | | | | | | | | | | |
| Schneider | MTN577199 | R.C | 20-315W | | | | | | | | | | | | | |
| Schneider | E3030HD | | 40W-600W | | | | | | | | | | | | | |
| Schneider | SBD-SPL | RL | 100W | | | | | | | | | | | | | |
| Schneider System M | MTN5140-0000 | RL | 100W | | | | | | | | | | | | | |
| Schneider Odace | S-5x0518 | RL | 100W | | | | | | | | | | | | | |
| Schneider Exxact | 1900910(SE) | RL | 100W | | | | | | | | | | | | | |
| Schneider Exxact | 2622161(FI) | RL | 100W | | | | | | | | | | | | | |
| Schneider Exxact | 1470207(NO) | RL | 100W | | | | | | | | | | | | | |
| Schneider | SND2200523 | RL | 500W | | 2-7 pcs | 2-7 pcs | | | 2-12 pcs | | | | | | | |
| Schneider | CCT011263 | RL | 315W | | | | | | | | | | | | | |
| Schneider Trend | ATTD1000RL | RL | 315W | | | | | | | | | | | | | |
| Schneider Trend | 1370814 | RL | 315W | | | | | | | | | | | | | |
| Schneider Artic | 3512423 | RL | 315W | | | | | | | | | | | | | |
| Schneider Artic | 1471021 | RL | 315W | | | | | | | | | | | | | |
| Schneider Exxact | 1900913(SE) | RL | 315W | | | | | | | | | | | | | |
| Schneider Exxact | 2622008(FI) | RL | 315W | | | | | | | | | | | | | |
| Schneider Exxact | 1470216(NO) | RL | 315W | | | | | | | | | | | | | |
| Schneider Unica | MGU3.512.xx | RL | 315W | | | | | | | | | | | | | |
| Schneider Unica | MGU5.512.xx | RL | 315W | | | | | | | | | | | | | |
| Schneider | MTN5135-0000 | RL | 315W | | | | | | | | | | | | | |
| Schneider | CCT011723 | RLC | 600W | | | | | | | | | | | | | |
| Schneider | LTD600RCL | RLC | 600W | | | | | | | | | | | | | |
| Schneider Trend | 1370833 | RLC | 600W | | | | | | | | | | | | | |
| Schneider Artic | 3512448 | RLC | 600W | | | | | | | | | | | | | |
| Schneider Artic | 1471011 | RLC | 600W | | | | | | | | | | | | | |
| Schneider | CCT011533 | RC | 315W | | | | | | | | | | | | | |
| Schneider | MGU3.515.18 | RLC | 350W | | | | | | | | | | | | | |
| Schneider | CCT0115C3 | RC | 1000W | | | | | | | | | | | | | |
| Scholki/NOVUM | ETD U1 | RLC | 35-500W | | | | | | | | | | | | | |
| Siemens | 5TC8284 | RC | 20-600W | | | | | | | | | | | | | |
| VADSBO | LD 220 | RLC | 1-200W | | | | | | | | | | | | | |
| Varilight | IOI401M | ? | ? | | | | | | | | | | | | | |
| Varilight | IQT401M | RC | 400W | | | | | | | | | | | | | |
| Varilight | J401 | ? | 400/250W | | | | | | | | | | | | | |
| Varilight | V-Pro Z1J400M | RC | 400W | 1-11 | 6-10 | | | 1-16 | | 1-11 | | | | | | |
| VEILENDING | MDC-10-MH | | 10-420W | | | | 1 max | 2 max | | | | | | | | |
| VIKO | KARRE | RL | 600W | | | | | | | | | | | | | |
| VIKO | CARMEN BEYAZ | RL | 600W | 4 max | 4 max | | | | | 4 max | | | | | | |
| Vimar | EIKON 20160 | RL | 500W/300VA | 2 max | 2 max | | | | | 2 max | | | | | | |

(1) This dimmer has complex installation but works well under certain configurations