



Long handle, padlockable	2 - stay put		ZB4 BJ291	0.044
			ZB4 BJ292	0.044
			ZB4 BJ294	0.044
	2 - spring return from right to left		ZB4 BJ491	0.044
	3 - stay put		ZB4 BJ391	0.044
			ZB4 BJ392	0.044
			ZB4 BJ393	0.044
			ZB4 BJ394	0.044
			ZB4 BJ395	0.044
			ZB4 BJ396	0.044
			ZB4 BJ397	0.044
	3 - spring return to centre		ZB4 BJ593	0.044
	3 - spring return from right to centre		ZB4 BJ891	0.044
			ZB4 BJ893	0.044
			ZB4 BJ895	0.044
	3 - spring return from left to centre		ZB4 BJ792	0.044
			ZB4 BJ793	0.044
			ZB4 BJ796	0.044

(2) The symbol indicates the padlocking positions.

Padlockable long handle operator (6.35 mm shank max.) ZB4 BJ●9●

