

THICKNESS TABLE(mm)

Wall mounting steel enclosures

NSY CRN	Body	Back	Plein Door	Transparent Door
CRN-22/150 to CRN-108/300	1,2			
CRN-252/150 to CRN-66/300		1		
CRN-75/200 to CRN-108/300		1		
Doors models 22, 23, and 345			1,2	
Door model 2520			1	
Doors models 325, 33, 34, 43 and 44			1	1
Doors models 46, 54, 55, 64 and 65			1,2	1,2
Doors models 66, 68, 75, 86, 88, 106 and 108			1,5	1,5

cable entries

All Models

Thickness

1

NSY CRNG	Body	Back	Plein Door	Transparent Door
CRNG-86/400 to CRNG-1210/400	1,5			
CRNG-1012/400 to CRNG-1410/300	2			
CRNG-86/400 to CRNG-1210/400		1,5		
CRNG-1012/400 to CRNG-1410/300		2		
CRNG-86/400 to CRNG-1410/300			2	
CRNG-86/400 to CRNG-1410/300				2

cable entries

All Models

Thickness

1,5

Stainless steel enclosures (wall mounting and Floor standing)

NSYS3X 304L	Body	Back	Plein Door	Transparent Door
CRSX-32/150 to CRSX-64/200	1	1	1,2	1,5
CRSX-66/250	1	1	1,5	1,5
CRSX-75/250 to CRSX-128/300	1,2	1,2	1,5	1,5
CRSX-1010/300 to CRSX-1210/300	1,5	1,5	1,5	1,5

NSYS3X 316L	Body	Back	Plein Door	Transparent Door
CRSX-32/150 to CRSX-66/250	1	1	1,5	1,5
CRSX-75/250 to CRSX-1210/300	1,5	1,5	1,5	1,5

NSYSMX (CMOX)

All Models

Body	Back	Plein Door
2	2	2

NSYSFX (CLX)

All Models

Framework	Back	Side panels	Door
1,5	1,5	1,5	2

NSYSDX (PKPX)

All Models

Framework	Back panel	Console	Door
1,5	1,5	1,5	1,5

Floor standing steel enclosures

NSYSM (CMO)

All Models

Body	Back	Plein Door	Transparent Door
1,5	1,37	1,8	1,8

NSYSMHF (CMO-CEM)

All Models

Body	Back	Door
1,5	1,5	1,5

NSYSF (OLN)

All Models

Framework	Back	Side panels	Door	Transparent Door
1,5	1,5	1,5	1,8	1,8

NSYSFHF (OLN-CEM)

All Models

Framework	Back	Side panels	Door
1,5	1,5	1,5	1,5

NSYSD (PK / PKP)

All Models

Framework	Back panel	Console	Door
1,5	1,5	1,5	1,5

Accessories

Mounting plate WM

NSYMM2520 to MM75

NSYMM86 to MM1410

Thickness

1,8

2,5

Plein mounting plate FS

NSYMP (PMOL) up to 1000 mm. Width.

NSYMP (PMOL) 1200 mm Width to 1600

2,5

3

Plinth, side panels and Front

NSYSPF3100 to NSYSPS12200

1,5

Side panels SF

NSY2SP124 to NSY2SP228

1,5

Rear panel SF

NSYBP126 to NSYBP2212

1,5

Doors SF / SM

NSYSFD.....

1,8

Internal door SF / SM

NSYID166 to NSYID228

1,5

Internal door WM

NSYPIN43 to NSYPIN86

NSYPIN108 to NSYPIN128

1,2

1,5

Partial mounting plate

NSYSPMP2560 to NSYSPMP40160

2,5

Canopy SF / SM

NSYSC630 to NSYSC2460

1,5

Canopy WM

NSYTJ2015 to NSYTJ12040

1,5

Wall mounting steel enclosures

NSYS3DEX

S3DEX-32/150 to S3DEX-44/200

S3DEX-54/200

S3DEX-64/250

S3DEX-66/250

S3DEX-75/250

S3DEX-86/250 to S3DEX-108/300

Body Back Plein Door

1

1

1

1

1

1,2

1,2

1,2

1,2

1,15

1,15

1,2

1,2

1,2

1,2

1,15

1,15

1,5

Wall mounting steel enclosures

NSYS3D and NSYS3DC

	Body	Back	Plein Door	Transparent Door
S3D-32/150 to S3D-44/200	1	1	1	1
S3D-46/200 to 46/250	1,15	1,15	1,2	1,2
S3D-53/200 to S3D-55/200	1	1	1,2	1,2
S3D-64/200 to S3D-66/400	1,15	1,15	1,2	1,2
S3D-68/300	1,15	1,15	1,5	1,5
S3D-75/250	1,15	1,15	1,2	1,2
S3D-86/250 to 86/400	1,15	1,15	1,5	1,5
S3D-88/250 to 88/300	1,2	1,2	1,5	1,5
S3D-810/300 to 1010/300	1,45	1,45	1,5	1,5
S3D-1012/300 to 1012/400	1,5	1,5	2	2
S3D-126/300 to 1210/400	1,45	1,45	1,5	1,5
S3D-1212/300 to 1410/300	1,5	1,5	1,5	1,5

Accessories

cable entries

All Models

Thickness

1,5

Mounting plate WM

NSYMM22 to MM76

1,8

NSYMM86 to MM1410

2,5

Wall mounting steel enclosures

NSYS3HF

	Body	Back	Plein Door
S3HF-43/200 to S3HF46/200	1,2	1,2	1,2
S3HF-54/200 to S3HF64/200	1,2	1,2	1,2
S3HF-66/250 to S3HF128/300	1,5	1,5	1,5