



[TAG[MainCharacteristics]]

| | |
|-------------------|------------------------------|
| Range of product | NSX100...250 NSX400...630 |
| Device short name | 2 carriage switches |

[TAG[ComplemCharacteristics]]

| | |
|---|--|
| Auxiliary contacts type | Standard |
| Auxiliary contacts operation | CE/CD |
| [Ith] conventional free air thermal current | 6 A |
| [Ie] rated operational current | AC-12: 6 A AC 50/60 Hz 110 V AC-12: 6 A AC 50/60 Hz 220/240 V AC-12: 6 A AC 50/60 Hz 24 V AC-12: 6 A AC 50/60 Hz 380/440 V AC-12: 6 A AC 50/60 Hz 48 V AC-12: 6 A AC 50/60 Hz 480 V AC-12: 6 A AC 50/60 Hz 660/690 V AC-15: 0.1 A AC 50/60 Hz 660/690 V AC-15: 1.5 A AC 50/60 Hz 480 V AC-15: 2 A AC 50/60 Hz 380/440 V AC-15: 4 A AC 50/60 Hz 220/240 V AC-15: 5 A AC 50/60 Hz 110 V AC-15: 6 A AC 50/60 Hz 24 V AC-15: 6 A AC 50/60 Hz 48 V DC-12: 0.3 A DC 250 V DC-12: 0.6 A DC 110 V DC-12: 2.5 A DC 48 V DC-12: 6 A DC 24 V DC-14: 0.03 A DC 250 V DC-14: 0.05 A DC 110 V DC-14: 0.2 A DC 48 V DC-14: 1 A DC 24 V |
| Minimum load | 100 mA at 24 V DC |

[TAG[EnvCharacteristics]]

Offer Sustainability

| | |
|---|---|
| Not Green Premium product | Not Green Premium product |
| Compliant - since 0818 - Schneider Electric declaration of conformity | Compliant - since 0818 - Schneider Electric declaration of conformity |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|