



Main

Device short name	Motor mechanism module
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	Compact NSX circuit breaker Compact NSX DC circuit breaker circuit breaker
Product compatibility	PowerPact L-Frame
[In] rated current	400 A 630 A
[Uc] control circuit voltage	208...277 V AC 60 Hz 220...240 V AC 50/60 Hz

Complementary

Control type	Standard
Control signal type	Impulse Maintained
Mounting mode	Fixed
Response time	< 600 ms (opening) < 80 ms (closing)
Maximum operating frequency	4 per minute
Maximum power consumption in VA	500 VA closing 500 VA opening
Locking options description	Padlocking in OFF position 1 to 3 padlocks Ø 5 to Ø 8

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------