

STD100, 200, 500 & 660 Duct



STD100, 200, 500

STD 100, 200 and 500 temperature sensors are intended for air duct mounting. The STD housing is equipped with a Ø 20 mm (0.79 in.) cut-out for the cable, a 20 mm (0.79 in.) conduit gland nut and a mounting flange.

Accuracy See Appendix A: Tables A, B, C

Part number	Model number	Description	Probe length	System
5123002010	STD100-50	Duct Temperature Sensor STD100-50	50 mm (1.97 in.)	TAC Vista, TAC Xenta
5123004010	STD100-100	Duct Temperature Sensor STD100-100	100 mm (3.94 in.)	TAC Vista, TAC Xenta
5123006010	STD100-150	Duct Temperature Sensor STD100-150	150 mm (5.91 in.)	TAC Vista, TAC Xenta
5123008010	STD100-200	Duct Temperature Sensor STD100-200	200 mm (7.87 in.)	TAC Vista, TAC Xenta
5123010010	STD100-250	Duct Temperature Sensor STD100-250	250 mm (9.84 in.)	TAC Vista, TAC Xenta
5123012010	STD100-300	Duct Temperature Sensor STD100-300	300 mm (11.81 in.)	TAC Vista, TAC Xenta
5123014010	STD100-400	Duct Temperature Sensor STD100-400	400 mm (15.75 in.)	TAC Vista, TAC Xenta
5123030010	STD200-50	Duct Temperature Sensor STD200-50	50 mm (1.97 in.)	TAC I/NET
5123032010	STD200-100	Duct Temperature Sensor STD200-100	100 mm (3.94 in.)	TAC I/NET
5123034010	STD200-150	Duct Temperature Sensor STD200-150	150 mm (5.91 in.)	TAC I/NET
5123036010	STD200-200	Duct Temperature Sensor STD200-200	200 mm (7.87 in.)	TAC I/NET
5123038010	STD200-250	Duct Temperature Sensor STD200-250	250 mm (9.84 in.)	TAC I/NET
5123040010	STD200-300	Duct Temperature Sensor STD200-300	300 mm (11.81 in.)	TAC I/NET
5123042010	STD200-400	Duct Temperature Sensor STD200-400	400 mm (15.75 in.)	TAC I/NET
5123074010	STD500-150	Duct Temperature Sensor STD500-150	150 mm (5.91 in.)	Andover Continuum
5123078010	STD500-250	Duct Temperature Sensor STD500-250	250 mm (9.84 in.)	Andover Continuum
5123082010	STD500-400	Duct Temperature Sensor STD500-400	400 mm (15.75 in.)	Andover Continuum



STD660

The STD660 temperature sensor is intended for air duct mounting, and has a telescopic probe extendable from 100 to 300 mm (3.94 to 11.81 in.). The STD660 housing is equipped with a Ø 20 mm (0.79 in.) cut-out for the cable. A 20 mm (0.79 in.) conduit gland nut and a mounting flange are supplied with the product.

Accuracy See Appendix A: Table F

Part number	Model number	Description	Probe length	System
5126030000	STD660	Duct Temperature Sensor STD660	100 to 300 mm (3.94 to 11.81 in.)	Satchwell