

		Complementary accessories		KHZSP85 200	KHZSP85 300	KHZSP85 400	KHZSP85 500	KHZSP85 600	
Cable ladders									
KHZSP85 L = 3 m		Clamp 42 H85	T- bolt 26F	CSU795391	CSU795392	CSU795393	CSU795394	CSU795395	
KHZSP85 L = 6 m		Profile Clamp 42 ZM	M8x30	CSU795401	CSU795402	CSU795403	CSU795404	CSU795405	
KHZSPZ L = 3 m		U-bolt set M8 ø32 HDG	Screwset 22S						
KHZSPZ L = 6 m		U-bolt set M8 ø20-25							
Covers									
Cover W5-200 2 m				732265					
Cover W5-300 2 m					732266				
Cover W5-400 2 m						732267			
Cover W5-500 2 m							732268		
Cover W5-600 2 m								732269	
Cover clamp			713694						
Cover clamp H85			713694	CSU795454					
Profile support piece 37			713694						
Support									
Bracket 3 H85-200		CSU795436	734744	CSU795438					
Bracket 3 H85-300		CSU795436	734744		CSU795439				
Bracket 3 H85-400		CSU795436	734744			CSU795440			
Bracket 3 H85-500		CSU795436	734744				CSU795441		
Bracket 3 H85-600		CSU795436	734744					CSU795442	
Rail 24/48 attachment			713694	CSU795513					
Pendant/fix. rail 24/48 3 m			713694	705093					
Ceiling bracket 5			713694	718640					
Pendant joint 2FJ			713694	CSU795555					
Cantilever arm 50-200		CSU795241	734744	723434					
Cantilever arm 50-300		CSU795241	734744		723436				
Cantilever arm 50-400		CSU795241	734744			723437			
Cantilever arm 50-500		CSU795241	734744				723438		
Cantilever arm 50-600		CSU795241	734744					723439	
Angle bracket 5L			713694						
Direct wall fixation bracket			713694	CSU795466	CSU795466	CSU795466	CSU795466	CSU795466	
Joints & Couplings									
Joint 21 H85			713694	CSU795425					
Joint 21 screw-fixation ZM									
Coupling 22 H85			713694	CSU795468					
Junction coupling 14 H85			713694	CSU795557					
Coupling 22									
Junction coupling 14			713694						

	KHZSPZ 200	KHZSPZ 300	KHZSPZ 400	KHZSPZ 500	KHZSPZ 600
	CSU795430	CSU795431	CSU795432	CSU795433	CSU795434
	734494	734495	734496	734497	734498
	732265				
		732266			
			732267		
				732268	
					732269
	728584				
	730188				
	CSU795438				
		CSU795439			
			CSU795440		
				CSU795441	
					CSU795442
	CSU795513				
	705093				
			718640		
	CSU795555				
	723434				
		723436			
			723437		
				723438	
					723439
	731791				
	CSU795051				
	718409				
	725096				

		Complementary accessories		KHZSP85 200	KHZSP85 300	KHZSP85 400	KHZSP85 500	KHZSP85 600	
Cable ladders									
KHZSP85 L = 3 m		Clamp 42 H85	T- bolt 26F M8x30 HDG	CSU795391	CSU795392	CSU795393	CSU795394	CSU795395	
KHZSP85 L = 6 m		Profile Clamp 42 ZM		CSU795401	CSU795402	CSU795403	CSU795404	CSU795405	
KHZSPZ L = 3 m		U-bolt set M8 ø32 HDG	Screwset 22S HDG						
KHZSPZ L = 6 m		U-bolt set M8 ø20-25 HDG							
Rock Bolt									
Rock bolt attachment ø20-25 mm		CSU795523		CSU795511					
ø32 mm		CSU795523		CSU795535					
Security RB attachment ø20-25 mm		CSU795475		CSU795539					
ø32 mm		CSU795475		CSU795541					
Adj RB attachment ø20-25 mm		CSU795523		CSU795509					
ø32 mm		CSU795475		CSU795533					
Rock bolt connector ø20-25 mm		CSU795523		CSU795521					
ø32 mm		CSU795475		CSU795537					
Rock bolt side stabilizer plate				CSU795525					
Accessories									
Angle plate 33/2			713694						
Junction box plate 35P			713694						
Junction box plate 35S			713694						
Junction box plate 35S H85			713694	CSU795427					
Luminaire bracket H85 200			713694	CSU795444					
Luminaire bracket H85 300			713694		CSU795445				
Luminaire bracket H85 400			713694			CSU795446			
Luminaire bracket H85 500			713694				CSU795447		
Luminaire bracket H85 600			713694					CSU795448	
Camera attachment bracket KHZSP85			713694	CSU795517					
Camera attachment bracket R-Bolt			713694	CSU795560					
Camera attachment wall bracket			713694	CSU795561					
Heat detector installation plate			713694	CSU795519					

	KHZSP 200	KHZSPZ 300	KHZSPZ 400	KHZSPZ 500	KHZSPZ 600
	CSU795430	CSU795431	CSU795432	CSU795433	CSU795434
	734494	734495	734496	734497	734498
	CSU795511				
	CSU795535				
	CSU795539				
	CSU795541				
	CSU795509				
	CSU795533				
	CSU795521				
	CSU795537				
	CSU795525				
	707748				
	731745				
	731746				
	CSU795560				
	CSU795561				
	CSU795519				