



Common NetShelter Spare Parts

This document includes the common spare parts for the:

- NetShelter SX, AV and Networking cabinets
- NetShelter WX cabinets
- NetShelter VX cabinets
- NetShelter SV cabinets
- NetShelter CX cabinets: **Please see Knowledge Base document FA158648.**
- Discontinued NetShelter cabinets: EP, ES, VS
- Miscellaneous

NOTE: Side Panels, Roofs and Doors

Please use the replacement skus for side panels, roofs and doors. Do not use spare parts. Even if you need only one side panel or rear door and the replacement sku comes with two, please use the sku. To determine the correct sku please see the NetShelter Compatibility Chart. It's available to external customers on the APC website under Support / Search the Knowledge Base, then perform a search for FA158651.

NetShelter SX, AV, and Networking Cabinets

- Door and Side Panel Replacement Key: W870-8135 (single key).
- Door Handle: 840-0206B. (includes key). New door handle w/ no logo: 0J-840-0206B-002.
NOTE: AR3200 Colo cabinets use combination handles but they're not the exactly the same as AR8132A. Before replacing the door handle of an AR3200 please see Knowledge Base documents FA164127 and FA163953.
- Door and side panel key: W870-8135.
- Front door handle hasp: 870-11672B, screw 803-6044A.
- Literature kit: 0L1353C.
- Front Door APC Nameplate: 885-2625A. (also see Kbase FA242360) (Blank = AR7001X384, 40-pack)
- SX Hardware Bag: 0J-0M-6324C. (hole plug 870-0190)
- AV Hardware Bag: 0M-10684.
- Cage Nut Tool: 870-8137A.
- Baying Bracket Screw: 803-5006B. (if unavailable use the hardware bag)
- Baying Bracket: 870-11538.
- Leveling Foot: 825-0035C.
- Side Panel Latch: 0J-840-0269-333SE (set of 4).
- Castor for non-SP1/2 cabinets: use the replacement sku AR7719.
- Heavy duty swivel castor: 870-16002.
- Castor Nut: 803-2406A. (req. 4 per castor)
- PMA Screw: 803-8008A.
- SX Full Height Rail, 42U, 600 mm Wide, Square Holes, LEFT: 0J-0M-3951B.
- SX Full Height Rail, 42U, 600 mm Wide, Square Holes, RIGHT: 0J-0M-3952B.
- SX Full Height Rail, 42U, 750 mm Wide, Square Holes, LEFT: 0J-0M-6926D.
- SX Full Height Rail, 42U, 750 mm Wide, Square Holes, RIGHT: 0J-0M-6929D.
- SX Full Height Rail, 45U, 600 mm Wide, Square Holes, LEFT: 0M-11269A. (0J-0024 has left & right rails)
- SX Full Height Rail, 45U, 600 mm Wide, Square Holes, RIGHT: 0M-11271A. (0J-0024 has left & right rails)
- SX Full Height Rail, 45U, 750 mm Wide, Square Holes, LEFT: 0M-11275. (0J-0023A has left and right rails)
- SX Full Height Rail, 45U, 750 mm Wide, Square Holes, RIGHT: 0M-11273. (0J-0023A has left and right rails)
- SX Full Height Rail, 48U, 600 mm Wide, Square Holes, LEFT: 0M-5915C.
- SX Full Height Rail, 48U, 600 mm Wide, Square Holes, RIGHT: 0M-5916C.
- SX Full Height Rail, 48U, 750 mm Wide, Square Holes, LEFT: 0J-0M-6315C.
- SX Full Height Rail, 48U, 750 mm Wide, Square Holes, RIGHT: 0J-0M-6319C.
- Door Hinges: W0M-8869. (set of 4)
- Pallet Bracket: 0M-6943A. Sell screws 803-8579 if needed. Attaches bracket to pallet (2) and cabinet (2).
- Rear Door Rods, 42U: 0M-6485A.
- Rear Door Rod Pivot Pin: 870-8820. (cannot RMA this part, use rear door rod kit instead)

- Rear Door Rod Wire Hair Pin Clip: 840-0027A. (included in above 0M-6485A)
- Touch-up Paint Pen, Raven Black: 690-0108-001. White: 0J-690-0108-004.
- PMA Cover, 750 mm: 827-0191. (not for Networking cabinets)
- Door ground wires: 0W03571 and 0W03572, screw 803-6044A, washer 811-0805A.
- Front door handle hasp: 870-11672B, screw 803-0644A.
- SX Networking Air Block Kit: 0M-10457.
- Air block kit for 42U Networking Cabinet: 0M-10457.
- Air block kit for 48U Networking Cabinet: 0M-10804.
- VED Gasket: 0J-827-0292A. (8.4m) Enough Trim-Lok X5036BT for one complete cabinet. Black, Single. See FA315104 for installation instructions.

NetShelter WX AR100 AR100HD

- Door Handle & 2 Keys: 840-0103. (also included in 0M-7769 NetShelter WX Hardware Kit) (Key also works for NetShelter ES AR500)
- Hardware Bag: 0M-7773B.
- Manufacturing Hardware Kit: 0M-7769C. (includes 840-0712 locking rods, 840-0713 hinge, 803-0627A screws, 803-0006 caged nuts, 870-8492 key, 870-70620 rear locator, 840-0103 door handle)
- Front Door Hinge: 840-0713B, also requires (2) 811-0656 and (2) 803-6017A.
- Front Frame Hinge: 840-0713A.
NOTE: both 840-0713A and 840-0713B are included in 0M-7769C kit but no screw/washer for 840-0713B.
- Rear Door Hinge, TOP: 0M-7765B.
- Rear Door Hinge, BOTTOM: 0M-7764B.
- Rear Door Hinge Screw (req. 4 per hinge): 803-0627A.
- Touch-up Paint Pen, Raven Black: 690-0108-001.

NetShelter WX AR106, AR109, AR112

- Key W870-8135

NetShelter WX AR106SH4, AR109SH4, AR112SH4, AR106SH6, AR109SH6, AR109SH6, AR106V & AR106VI

- Key W870-8135
- Door Handle 0J-840-0206B-002
- Replacement Fan Module: 0J-0M-89059-115 (115V), 0J-0M-89059-230 (230V)

NetShelter VX

- Door Handle: 840-0717A. (no key)
- Side Panel Lock: 870-8540.
- Touch-up Paint Pen, Raven Black: 690-0108-001.
- Non-seismic 25U Side Panel: AR8382BLK.
- Non-seismic 42U Side Panel: AR8364BLK.
- Seismic 42U Left Hand Side Panel: AR8392BLK.
- Seismic 42U Right Hand Side Panel: AR8393BLK.
- Rear Door 42U, 600 mm: AR8362BLK.
- Rear Door 42U, 750 mm: AR8370BLK.
- Front Door 42U, 600 mm: AR8361BLK.
- Front Door 42U, 750 mm: AR8369BLK.
- Front Door Hinge Pin: 870-8115A, clip 840-0027A, Spring 840-0023
- Roof AR8360BLK.
- Seismic Roof: AR8391BLK.
- Front Door Hinge Pin: 870-8115A, Clip: 840-0027A, Spring: 840-0023.
- Castor: 0J-870-8133. (set of 2)
- Key: W870-8135.

NetShelter SV

- Key W870-8135
- Bolt Down Pallet Bracket: 0M-816057.
- Pallet Bracket Hardware, Screw to Cabinet: 803-6044A, Screw to Pallet: 803-4825A, Washer to Pallet: 811-0805A.
NOTE: To connect a pallet bracket to the cabinet requires one (1) 803-6044A.

NOTE: To connect a pallet bracket to the cabinet and the pallet requires one (1) 803-6044A, one (1) 803-4825A, one (1) 811-0805A.

- Top/Bottom Cable Accessory Panel: 870-23243.
- M6 Serrated Flange Washer: 811-0604A.
- Joining Bracket 600 mm: 870-23258.
- Joining Bracket 24 inch: 870-23904.
- Door Hinge Pin Bushing: 876-0993.
- Door Hinge Pin Washer 6 mm: 876-0995.
- Door Hinge Hole Plug: 876-0992.
- Equipment Mounting Rails, 42U, LH: 0M-77398.
- Equipment Mounting Rails, 42U, RH: 0M-77399.
- Equipment Mounting Rails, 48U, LH: 0M-77401.
- Equipment Mounting Rails, 48U, RH: 0M-77400.
- Castor: 870-23432.
- Leveling Foot: 825-0035C.
- Side Panel Lock: 840-9051.
- Side Panel Latch: 876-0996.
- Door Handle: 840-9053.

NOTE: The SX door handle can also be used but the hasp from the rear of the SV door handle must be used. Also, the SX door handle has the APC logo, the SV does not.

- Door Handle Hasp Rubber Filler: 876-1004.
- Combination Tool M6/T30: 815-7029.
- Rear Door Rods 42U: 0M-816023.
- Rear Door Rods 48U: 0M-816010.

NetShelter CX Please see Knowledge Base document FA158648.

The Knowledge Base can be found on your local APC website. Choose the Support tab, then Support, then FAQs. Search on document number FA158648.

NetShelter EP (AR1000-series)

- Key: W870-8135.
- Door Handle: 840-0717A.
- Hinge L-pin: 870-8115A.
- Coil Spring: 840-0023.
- Wire Hair Pin: 840-0027A.
- 42U Side Panel: AR8333 (BLK).
- 22U Side Panel: AR8338 (BLK).
- 42U Rear Door: AR8332 (BLK).
- 22U Rear Door: AR8337 (BLK).
- 42U Front Door: AR8331 (BLK).
- 22U Front Door: AR836 (BLK).
- 42U Roof: AR8330 (BLK).
- 22U Roof: AR8341 (BLK).

NetShelter ES (AR500-series)

- Front Door Handle: 840-0103.
- Key: 0J-870-8492.
- Side Panel: AR8353 – Discontinued.
- Side Panel Lock: 870-8335 – Discontinued.

NetShelter VS (AR2800-series)

- Key: W870-8135.
- Front Door Handle: 840-0717A.
- 42U Side Panel: AR8384BLK.
- Rear Door 42U: AR8362BLK.
- Front Door 42U: AR8361BLK.
- Sides: AR8384BLK.

Miscellaneous

- Red Key #300 for ISX PDU: 0J-870-5157.
- PSX Rack ID Label Kit: 885-1353A.
- AR204A Hardware Bag: W0M-9716.
- AR203A Hardware Bag: 0M-9696.
- Ladder Grounding Kit: 1 ground wire, 2 pain piercing washers and nuts; 0M-1352A.

Uncontrolled if printed. Electronic Storage and Reference Recommended.

REV.17 20120424