



产品认证证书

证书编号: CQC2008010305267939

申请人名称及地址

施耐德电气(中国)有限公司上海分公司
上海市普陀区绥德路669号

制造商名称及地址

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

生产企业名称及地址

SCHNEIDER ELECTRIC INDUSTRIES SA(V054246)
52 Rue De Dion Bouton ZI Nord F-87280 LIMOGES France

产品名称和系列、规格、型号

安全限位开关

XCSE: Ui:500V; Uimp:4kV; Ith:6A; AC-15:Ue/Ie:24V/6A,48V/6A,120V/3A,240V/1.5A
DC-13:Ue/Ie:24V/0.55A,48V/0.55A,125V/0.55A; IP67; 详细型号解释见附件

产品标准和技术要求

GB/T 14048.5-2017

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462142-2019 认证规则的要求, 特发此证。

发证日期: 2020年08月25日 有效期至: 2024年09月24日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任:

陆楠



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0372777



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2008010305267939

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND ADDRESS OF THE FACTORY

SCHNEIDER ELECTRIC INDUSTRIES SA (V054246)
52 Rue De Dion Bouton ZI Nord F-87280 LIMOGES France

PRODUCT NAME, MODEL AND SPECIFICATION

Safety Limit Switch

XCSE: Ui:500V; Uimp:4kV; Ith:6A; AC-15:Ue/Ie:24V/6A,48V/6A,120V/3A,240V/1.5A
DC-13:Ue/Ie:24V/0.55A,48V/0.55A,125V/0.55A; IP67

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

TYPE OF CERTIFICATION SCHEMES

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462142-2019 .

Valid from: Aug.25,2020

Valid until: Sep.24,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0372777



产品认证证书

附录

第 1 页 共 2 页

证书编号: CQC2008010305267939

纸号: 372777

型号解释:

	$\frac{XCS}{I}$	$\frac{E}{II}$	$\frac{7}{III}$	$\frac{3}{IV}$	$\frac{1}{V}$	$\frac{3}{VI}$	$\frac{7}{VII}$
I-	产品型号 XCS 安全限位开关						
II-	联锁形式 E - 有锁, 电磁解锁						
III-	触头形式 5-1 NC+2 NO 7-2 NC+1 NO 8-3 NC						
IV-	电磁铁解锁 3- 电磁铁得电解锁 5-电磁铁失电解锁						
V-	电磁铁和 LED 电压 1--24 V ac/dc 2-48 V ac/dc 3-110-120 V ac/dc 4-220-240 V ac/dc						
VI-	接口形式 1-13 号欧洲电缆密封管螺纹孔 2-ISO 电缆密封管螺纹孔 3-1/2 in. NPT 螺纹孔						
VII-	电磁铁中触头形式 空白 --- 1NC+1NO 7 --- 2NC						

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 2 页 共 2 页

证书编号: CQC2008010305267939

纸号: 372777

XCS
I

E
II

7
III

3
IV

1
V

3
VI

7
VII

- I- Product type
XCS safety limit switch
- II- Type of interlocking
E-with interlocking, locking by electromagnet
- III- Type of contact block
5 - 1 NC + 2 NO
7 - 2 NC + 1 NO
8 - 3 NC
- IV- Type of interlocking
3 - On energization
5 - On de-energization
- V- Electromagnet and LED supply voltage
1--24 V ac/dc
2 - 48 V ac/dc
3 - 110-120 V ac/dc
4 - 220-240 V ac/dc
- VI- Type of entry
1 - Threaded hole for Type 13 European cable gland
2 - Threaded hole for ISO cable gland
3 - 1/2 in. NPT threaded hole
- VII- additive contact block
Blank --- 1NC+1NO
7 --- 2NC

注: 此附录与证书同时使用时有效。

主任: _____

陆杨



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>