

NSYTRACE24

END COVER, 2 LEVEL, 4PTS, 2,2MM WIDTH,
FOR SCREW TERMINALS NSYTRV24D,



Main

Range	Linergy
Product name	Linergy TR
Product or component type	Cover plate
Device short name	TRA
Accessory / separate part category	Insulation accessory
Product compatibility	TRV screw terminal terminal block
Thickness	2.2 mm

Complementary

Cable cross section	2.5 mm ² 4 mm ²
Number of connections	2
Number of measurement input	4 2
Quantity per set	Set of 50
Net weight	2.2 g
Colour	Grey

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4 g
Package 1 Height	4 cm
Package 1 width	14 cm
Package 1 Length	27 cm
Unit Type of Package 2	BAG

Number of Units in Package 2	50
Package 2 Weight	226 g
Package 2 Height	5 cm
Package 2 width	12.5 cm
Package 2 Length	27 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	50
Package 3 Weight	234 g
Package 3 Height	6.2 cm
Package 3 width	11.8 cm
Package 3 Length	19 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------