

Thalassa boxes

Selection guide

PB500090



PB500091-32



Overall external dimensions			Overall internal dimensions			Body	Cover	Minor pack.	Cover screw	Universal boxes with IP66		
(mm)			(mm)			(mm)	(mm)				PC-UL IP66 IK08	
Height	Width	Depth	Height	Width	Depth						Opaque cover	Transparent cover
74	74	54	65	65	47	37	10	5	Metal		NSYBTP775	-
89	89	54	80	80	47	37	10	5	Metal		NSYBTP885	-
116	74	62	105	65	55	45	10	5	Metal		NSYBTP1176	-
		94	105	65	85	45	40	3	Metal		-	-
	116	62	105	105	55	45	10	5	Plastic		NSYBTP11116	-
133		105	105	125	45	80	2	Plastic		-	-	
138	93	72	125	80	65	45	20	2	Plastic		NSYBTP1397	NSYBTP1397T
164	121	87	150	105	80	60	20	2	Plastic		NSYBTP16128	NSYBTP16128T
192	121	87	175	105	80	60	20	2	Plastic		NSYBTP19128	NSYBTP19128T
		105	175	105	100	60	40	2	Plastic		NSYBTP191210H	NSYBTP191210HT
	164	87	175	150	80	60	20	1	Plastic		NSYBTP19168	NSYBTP19168T
105		175	150	100	60	40	1	Plastic		NSYBTP191610H	NSYBTP191610HT	
241	194	87	225	175	80	60	20	1	Plastic		NSYBTP24198	NSYBTP24198T
		107	225	175	100	80	20	1	Plastic		NSYBTP241910	NSYBTP241910T
		107	225	175	100	60	40	1	Plastic		NSYBTP241910H	NSYBTP241910HT
		127	225	175	120	80	40	1	Plastic		NSYBTP241912H	NSYBTP241912HT
291	241	88	275	225	80	60	20	1	Plastic		NSYBTP29248	NSYBTP29248T
		128	275	225	120	100	20	1	Plastic		NSYBTP292412	NSYBTP292412T
		128	275	225	120	60	60	1	Plastic		NSYBTP292412H	NSYBTP292412HT
		168	275	225	160	100	60	1	Plastic		NSYBTP292416H	NSYBTP292416HT
341	291	128	325	275	120	100	20	1	Plastic		NSYBTP342912	NSYBTP342912T
		168	325	275	160	100	60	1	Plastic		NSYBTP342916H	NSYBTP342916HT