



Main

Range of product	Altivar
Range compatibility	Altivar 212 Altivar 32 Altivar Process ATV600 Altivar Machine ATV340 Altivar Lift Altivar 312 Solar Altivar 61Q Altivar Easy 610 Altivar Process ATV900 Lexium 32 Altivar 71Q Altivar 312 Altivar 71 Altivar Machine ATV320 Altivar 61
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To display the current values To control, adjust and configure the drive To save and download configurations
IP degree of protection	IP65

Complementary

Language	Chinese Finnish Hungarian Estonian English Romanian Norwegian Italian Slovak Turkish Polish Czech Bulgarian Dutch Portuguese Spanish German Korean Danish Lituanien Brazilian Greek Taiwanese Swedish French Russian
Realtime clock	Built-in
Battery size	CR2032
Battery life	10 yr
Display type	Backlit LCD screen white and red
Messages display capacity	8 lines
Pixel resolution	240 x 160
Product weight	0.2 kg

Environment

Ambient air temperature for operation	> -15...50 °C
---------------------------------------	---------------
