

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Uninterruptible Power Supplies
Name and address of the applicant	Schneider Electric IT Corporation, FKA APC American Power Conversion 132 Fairgrounds Road, PO Box 278, West Kingston, Rhode Island, 02892 USA
Name and address of the manufacturer	Schneider Electric IT Corporation, FKA APC American Power Conversion 132 Fairgrounds Road, PO Box 278, West Kingston, Rhode Island, 02892 USA
Name and address of the factory <small>Note: When more than one factory, please report on page 2</small>	Schneider Electric IT Business India Private Limited, FKA APC American Power Conversion NO 71 DODDATHOGURE VILLAGE ELECTRONIC CITY BEGUR HOBLI BANGALORE KA 561229 INDIA <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2 & 3
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 2
Model / Type Ref.	Galaxy VS
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62040-1:2008/A1:2013. National Differences specified in the CB Test Report. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62040-1:2008/AMD1:2013, IEC 62040-1:2008
As shown in the Test Report Ref. No. which forms part of this Certificate	4788871319 issued on 2019-02-12

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-02-19

Signature:

Jan-Erik Storgaard

Factories:

APC INDIA PVT LTD
 NO 18A SUVEY NO 128 1ST PHASE JIGANI INDUSTRIAL AREA JIGANI VILL. JIGANI HOBIL ANEKALTALUK
 BANGALORE KA 562106
 INDIA

Schneider Electric IT Business India Private Limited, FKA APC American Power
 EHPT UNIT 187/3 & 188/3 JIGANI HOBILI, JIGANI VILLAGE ANEKAL TALUK BANGALORE KA 562106
 INDIA

Ratings:

Configuration 10 kW/kVA 200V/208V/220

Input: 200 V / 208 V / 220 V, 37 A / 36 A / 34 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 29 A / 28 A / 27 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 200 V / 208 V / 220 V, 29 A / 28 A / 26 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 10 kW/kVA
 Neutral: 50 A/48 A /45 A

Configuration 15 kW/kVA 200V/208V/220

Input: 200 V / 208 V / 220 V, 56 A / 54 A / 51 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 44 A / 42 A / 40 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 200 V / 208 V / 220 V, 43 A / 42 A / 39 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 15 kW/kVA
 Neutral: 75 A / 72 A / 68 A

Configuration 20 kW/kVA 200V/208V/220V

Input: 200 V / 208 V / 220 V, 74 A / 72 A / 68 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 58 A / 56 A / 53 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 200 V / 208 V / 220 V, 58 A / 56 A / 52 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 20 kW/kVA
 Neutral: 100 A / 96 A / 91 A

Configuration 20 kW/kVA 380V/400V/415V

Input: 380 V / 400 V / 415 V, 38 A / 36 A / 35 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 380 V / 400 V / 415 V, 31 A / 29 A / 28 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 380 V / 400 V / 415 V, 30 A / 29 A / 28 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 20 kW/kVA
 Neutral: 53 A / 50 A / 48 A

Configuration 20 kW/kVA 480V

Input: 480 V, 30 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 480 V, 24 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 480 V, 24 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 20 kW/kVA
 Neutral: 42 A

Configuration 25 kW/kVA 200V/208V/220V

Input: 200 V / 208 V / 220 V, 91 A / 90 A / 85 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 73 A / 70 A / 66 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 200 V / 208 V / 220 V, 72 A / 69 A / 66 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 25 kW/kVA
 Neutral: 125 A / 120 A / 114 A

Configuration 30 kW/kVA 200V/208V/220V

Input: 200 V / 208 V / 220 V, 112 A / 107 A / 102 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 87 A / 84 A / 80 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 200 V / 208 V / 220 V, 87 A / 83 A / 79 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 30 kW/kVA
 Neutral: 150 A / 144 A / 136 A

Configuration 30 kW/kVA 380V/400V/415

Input: 380 V / 400 V / 415 V, 57 A / 54 A / 52 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 380 V / 400 V / 415 V, 46 A / 44 A / 42 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 380 V / 400 V / 415 V, 46 A / 43 A / 42 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 30 kW/kVA
 Neutral: 79 A / 75 A / 72 A

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/incbnames

Date: 2019-02-19

Signature: 
 Jan-Erik Storgaard

Configuration 30 kW/kVA 480V

Input: 480 V, 45 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 480 V, 36 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 480 V, 36 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 30 kW/kVA
 Neutral: 62 A

Configuration 40 kW/kVA 200V/208V/220V

Input: 200 V / 208 V / 220 V, 149 A / 143 A / 135 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 117 A / 112 A / 106 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 200 V / 208 V / 220 V, 115 A / 111 A / 105 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 30 kW/kVA
 Neutral: 200 A / 192 A / 182 A

Configuration 40 kW/kVA 380V/400V/415V

Input: 380 V / 400 V / 415 V, 76 A / 72 A / 69 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 380 V / 400 V / 415 V, 61 A / 58 A / 56 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 380 V / 400 V / 415 V, 61 A / 58 A / 56 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 40 kW/kVA
 Neutral: 105 A / 100 A / 96 A

Configuration 40 kW/kVA 480V

Input: 480 V, 60 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 480 V, 49 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Output: 480 V, 48 A, 50/60 Hz, 3ph+N+PE or 3ph+PE, 40 kW/kVA
 Neutral: 83 A

Configuration 50 kW/kVA 200V/208V/220V

Input: 200 V / 208 V / 220 V, 182 A / 179 A / 169 A, 50/60 Hz, 3ph+N+PE or 3ph+PE
 Bypass: 200 V / 208 V / 220 V, 146 A / 140 A / 133 A,

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-02-19

Signature:

Jan-Erik Storgaard