



## Main

Range	PowerLogic
Product name	PowerLogic PM8000
Device short name	PM8244
Product or component type	Power meter

## Complementary

Power quality analysis	Waveform capture Harmonic distortion Programmability (logic and math functions) Voltage sag and swell detection Up to the 63rd harmonic Compliance report EN 50160 Power quality monitoring IEC 62586 Power quality measurement IEC 61000-4-30 : class S
Device application	WAGES metering Power monitoring
Type of measurement	Power factor (total) Apparent power (total) Active and reactive power (total) Active and reactive power (per phase, rms) Apparent power (per phase, rms) Power factor (per phase, rms) Voltage Current Frequency
[Us] rated supply voltage	90...415 V AC +/- 10 % (45...65 Hz) 120...300 V DC +/- 10 %
Network frequency	60 Hz 50 Hz
[In] rated current	1 A 5 A 10 A
Poles description	1P + N 3P + N

3P

Power consumption in VA	18 VA at 415 V AC
Max power consumption in VA	36 VA at 415 V AC
Display type	Remote LCD display
Display resolution	320 x 240 pixels QVGA
Sampling rate	256 samples/cycle
Measurement current	50...10000 mA
Analogue input type	Current (impedance 0.3 mOhm) Voltage (impedance 5 MOhm)
Measurement voltage	57...400 V AC 42...69 Hz between phase and neutral 100...690 V AC 42...69 Hz between phases
Frequency measurement range	42...69 Hz
Number of inputs	3 digital 30 V AC 3 digital 60 V DC
Measurement accuracy	+/- 0.2 % active energy +/- 0.1 % voltage +/- 0.1 % current
Accuracy class	Class 0.2 (active energy according to ANSI C12.20) Class 0.2S (active energy according to IEC 62053-22) Class 0.2 (active power according to IEC 61557-12) Class 0.5S (reactive energy according to IEC 62053-24) Class 0.5 (power factor according to IEC 61557-12) Class 0.2 (voltage according to IEC 61557-12) Class 0.2 (current according to IEC 61557-12)
Number of outputs	1 pulse
Information displayed	Voltage Current Frequency Power Energy consumption Harmonic distortion
Communication port protocol	DNP3 IEC 61850 Modbus RTU 2-wire, : 115 kbauds, ION 2-wire, : 115 kbauds, Modbus TCP/IP Ethernet Modbus TCP/IP daisy chain : 10/100 Mbit/s, RSTP 801.1d 2004
Communication port support	Ethernet RS485 (screw terminal block)
Data recording	Waveform logs Sequence of event recording Data logs Harmonics logs Sag and swell logs Time stamping Min/Max of instantaneous values Alarm logs Event logs Trending/Forecasting GPS synchronisation
Memory capacity	512 MB
Web services	HTTP server Customizable home page File upload/download via FTP Alarm notification by e-mail
Communication service	SNMP NTP time synchronization SMTP e-mail notification RSTP support
Mounting mode	Flush-mounted Clip-on
Mounting support	DIN rail (meter device) Framework (remote display)
Provided equipment	Remote display

Installation category	III
Isolation voltage	IEC 61010-1 : CAT III, 400...690 V ed. 3 EN 61010-1 : CAT III, 400...690 V ed. 3 UL 61010-1 : CAT III, 347...600 V ed. 3 CSA C22.2 No 61010-1 : CAT III, 347...600 V ed. 3
Standards	IEC 62053-24 IEC 62053-22 IEC 61557-12 IEC 62052-11
Product certifications	N998 China RoHS CULus CE
Width	90.5 mm
Depth	90.8 mm
Height	90.5 mm
Product weight	528 g

## Environment

Electromagnetic compatibility	<ul style="list-style-type: none"> <li>• electrical fast transient/burst immunity test, conforming to IEC 61000-4-4</li> <li>• conducted RF disturbances, conforming to IEC 61000-4-6</li> <li>• immunity to impulse waves, conforming to IEC 61000-4-12</li> <li>• radiated radio-frequency electromagnetic field immunity test, conforming to IEC 61000-4-3</li> <li>• voltage dips and interruptions immunity test, conforming to IEC 61000-4-11</li> <li>• electrostatic discharge, conforming to IEC 61000-4-2</li> <li>• surge immunity test, conforming to IEC 61000-4-5</li> <li>• magnetic field at power frequency, conforming to IEC 61000-4-8</li> <li>• conducted and radiated emissions, conforming to EN 55022</li> <li>• conducted and radiated emissions, conforming to EN 55011</li> <li>• conducted and radiated emissions, conforming to FCC Part 15</li> <li>• conducted and radiated emissions, conforming to ICES-003</li> <li>• conducted RF disturbances 2...150 Hz, conforming to CLC/TR 50579</li> <li>• surge withstand, conforming to IEEE C37.90.1</li> </ul>
IP degree of protection	IP30 conforming to IEC 60529
Relative humidity	5...95 %
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	3000 m

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1425 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">End of life manual</a>
Product end of life instructions	Available