



Main

Range of product	INS320...630
Range	Compact
Device short name	INS320
Product or component type	Changeover switch
Device application	Change source of supply
Range compatibility	Compact INS INS320 switch disconnecter
Poles description	3P
Network type	AC DC
Network frequency	50/60 Hz
Mounting mode	Fixed
Upside connection	Front
Downside connection	Front
Suitability for isolation	Yes
Contact position indicator	Yes
[Icm] rated short-circuit making capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 50 kA switch-disconnector alone 690 V AC at 50/60 Hz

Complementary

Transfer switch class	PC
Number of contact position	3
Control type	Direct front rotary handle
Mounting support	Plate Rail
Locking options description	Padlocking in OFF position
[Ie] rated operational current	AC-22A: 320 A AC 50/60 Hz 220/240 V AC-22A: 320 A AC 50/60 Hz 380/415 V AC-22A: 320 A AC 50/60 Hz 440/480 V AC-22A: 320 A AC 50/60 Hz 480 V NEMA AC-22A: 320 A AC 50/60 Hz 500/525 V AC-22A: 320 A AC 50/60 Hz 660/690 V AC-23A: 320 A AC 50/60 Hz 220/240 V AC-23A: 320 A AC 50/60 Hz 380/415 V AC-23A: 320 A AC 50/60 Hz 440/480 V AC-23A: 320 A AC 50/60 Hz 480 V NEMA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

AC-23A: 320 A AC 50/60 Hz 500/525 V
 AC-23A: 320 A AC 50/60 Hz 660/690 V
 DC-22A: 320 A DC 125 V 2 poles in series
 DC-23A: 320 A DC 125 V 2 poles in series

[I _{th}] conventional free air thermal current	320 A at 60 °C
Rated duty	Uninterrupted
Intermittent duty class	Class 120 - 60 %
[U _i] rated insulation voltage	750 V AC 50/60 Hz
[U _{imp}] rated impulse withstand voltage	8 kV
[U _e] rated operational voltage	125 V DC conforming to IEC 60947-3 690 V AC 50/60 Hz conforming to IEC 60947-3 750 V AC 50/60 Hz conforming to IEC 60947-3 750 V DC conforming to IEC 60947-3
Mechanical interlocking	With mechanical interlocking
Mechanical durability	10000 cycles
Electrical durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz DC-23A: 1000 cycles 125 V DC 2 poles in series
Connection pitch	45 mm
[I _{cw}] rated short-time withstand current	11.5 kA during 3 s conforming to IEC 60947-3 20 kA during 1 s conforming to IEC 60947-3 4 kA during 30 s conforming to IEC 60947-3 4.9 kA during 20 s conforming to IEC 60947-3
Height	205 mm
Width	395 mm
Depth	155 mm
Net weight	13.5 kg

Environment

Standards	IEC 60947-3 IEC 60947-1
Product certifications	KEMA-KEUR CCC
Electrical shock protection class	Class II
IP degree of protection	IP40 conforming to IEC 60947-3
Pollution degree	3
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

Contractual warranty

Warranty	18 months
----------	-----------