

# DATASHEET

## 3025USB2-VW

Iconic Twin Socket Outlet with Twin USB charger – Vivid White, preassembled.

### Application

The twin Iconic GPO with twin USB charger comprises a Twin 10A socket outlet with an additional 2 USB charging stations, provided by the dual port 2x2.1A USB charging mechanism. The USB charger includes patented current management technology which reduces the output current to prevent overheating while minimising charge times. The dual USB chargers in the twin GPO eliminate the need for a power board or the manufacturer's original supplied charger. The energy-efficient USB Charger Mechs are compatible with both Apple® and Android™ devices, and use less than 0.07W of power while in Standby mode.



The 3025USB2-VW model is available in Vivid White Only. Other colour combinations can be configured from three products: 3025XUAG (grid), 3025CA-XX (Skin) and 42E2USBCAP-XX (USB Cap) – where XX represents the colour options: CY (Cool Grey), WY (Warm Grey) and AN (Anthracite).

### Features

- Slim Modern Styling with matte finish
- USB charger Mech - 2.1A per port in single mechanism (3.1A Max)
- Patented over temperature current management (windback)
- Patented 180° rotatable head on USB mech
- Safety shutters on the Socket outlets
- Easy to wire with inline floating wrapper terminals



40E2USBCAP – USB Cap available in four colours



Life Is On

**CLIPSAL**  
by Schneider Electric

## Specifications – Double Switched GPO Outlet

<b>Ground lug position</b>	Straight 180° position
<b>Mounting mode</b>	Horizontal
<b>Rate current</b>	10A for socket
<b>Rated operational voltage</b>	250V AC 50Hz
<b>Ambient air temp for operation</b>	0- 45°
<b>Service life in cycles</b>	12,000 cycles
<b>Electrical durability</b>	12,000 cycles
<b>Connection – terminals</b>	Screws
<b>Number of terminals</b>	3
<b>Material</b>	PC (polycarbonate) for skin ABS (acrylonitrile butadiene-styrene) for skin PC (polycarbonate) for grid plate PP (polypropylene) for flaps POM (polyoxymethylene) for shutter POM (polyoxymethylene) for locking bar
<b>Dimensions</b>	Plate: 120 mm H x 78mm W x 44mm D
<b>Outlet poles configuration</b>	1P + E with shutter

## Specifications – USB Mech

<b>Output current</b>	Max 2.1A per port (Max 3.1A for the module)
<b>Port Type</b>	2x USB A
<b>Standby Power</b>	< 70mW
<b>Efficiency</b>	> 78%
<b>Charging</b>	BC 1.2 and cable compensation for optimised charge times
<b>Ambient Operating Humidity</b>	5%-90% Relative Humidity, Non-condensing
<b>Input Connections</b>	120mm fly leads, 22AWG (064mm dia, 0.33mm <sup>2</sup> )
<b>IP rating</b>	IP20 Indoor Use Only
<b>Rating head angle</b>	180°
<b>Lifetime insertion of USB</b>	10,000 cycles
<b>Depth from rear of plate</b>	55mm (suits deep wall boxes)
<b>Compatibility</b>	Most Apple® and Android™ devices, including tablets and smart phones

Schneider Electric (Australia) Pty Ltd

Contact us: [clipsal.com/feedback](http://clipsal.com/feedback)

National Customer Care Enquiries:

Tel 1300 2025 25 Fax 1300 2025 56

New Zealand National Customer Care Enquiries:

Tel 0800 652 999 Fax 0800 101 152

Life Is On

**CLIPSAL**  
by Schneider Electric

Schneider Electric (Australia) Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this catalogue are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

© 2015 Schneider Electric. All Rights Reserved.

Trademarks are owned by Schneider Electric Industries SAS or its affiliated companies.