

TeSys DC Coil Specifications - LC1D09 thru LC1D38

Voltage Code	Resistance Ohms (Approx + or - 10%)	Inductance	Voltage
AD	4.41	0.18	5
AL	9.51	0.37	5
BD	101.9	3.9	24
BL	213.7	8.4	24
CD	207.7	8.1	36
CL	494.8	19	36
DD	1527	55	96
DL	3255	122	96
ED	392.7	15	48
EL	843.6	33	48
FD	2085	78	110
FL	4584	163	110
GD	2539	94	125
JD	26	1	12
JL	53.4	2.1	12
KD	1661	62	100
LD	6262	207	200
MD	7472	268	220
ML	17824	604	220
ND	633.3	24	60
PD	3923	143	155
QD	4845	177	174
RD	29692	1039	440
SCD	50973	1653	575
SD	819.9	31	72
SL	1953	71	72
TD	14986	526	305
UD	9580	345	250
UL	22158	745	250
VD	18944	659	348
XD	59146	2053	600
ZD	66.4	2.6	20
ZL	147.6	5.5	20