



产品认证证书

证书编号: CQC2007010305236411

申请人名称及地址

施耐德电气(中国)有限公司上海分公司
上海市普陀区绥德路669号

制造商名称及地址

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Reuil-Malmaison, France

生产企业名称及地址

SCHNEIDER ELECTRIC INDUSTRIES SA(V054246)
52 Rue De Dion Bouton ZI Nord F-87280 LIMOGES France

产品名称和系列、规格、型号

安全限位开关

XCS-PA, PL, PR, TA, TL, TR; 详情及型号解释详见附件

产品标准和技术要求

GB/T 14048.5-2017

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462142-2019 认证规则的要求, 特发此证。

发证日期: 2020年08月25日 有效期至: 2024年09月24日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任:

陆楠



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0372775



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2007010305236411

NAME AND ADDRESS OF THE APPLICANT

Schneider Electric (China) Co. Ltd. Shanghai Branch
No. 669, Suide Road, Putuo District, Shanghai, China

NAME AND ADDRESS OF THE MANUFACTURER

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

NAME AND ADDRESS OF THE FACTORY

SCHNEIDER ELECTRIC INDUSTRIES SA (V054246)
52 Rue De Dion Bouton ZI Nord F-87280 LIMOGES France

PRODUCT NAME, MODEL AND SPECIFICATION

Safety Limit Switch
XCS-PA, PL, PR, TA, TL, TR; See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

TYPE OF CERTIFICATION SCHEMES

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462142-2019 .

Valid from: Aug.25,2020

Valid until: Sep.24,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0372775



产品认证证书

附录

第 1 页 共 5 页

证书编号: CQC2007010305236411

纸号: 372775

XCS-PA, PL, PR, TA, TL, TR

Ith, Uimp, Ui, Ue, Ie 见下表:

	Ui	Ith	Uimp	使用类别: Ue, Ie
XCS-P.1, 2, 5, 6, 7 XCS-T.5, 7, 8	500V	10A	6kV	AC-15:Ue=240V,Ie=3 A DC-13:Ue=250V,Ie=0.27 A
XCS-P.3, 4, 8, 9	400V	6 A	4kV	AC-15:Ue=240V, Ie=1.5A DC-13:Ue=250V, Ie=0.1A

IP67

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 2 页 共 5 页

证书编号: CQC2007010305236411

纸号: 372775

型号解释:

XCS-P	Δ	5	9	1
I	II	III	IV	V

- I- 产品基本型号
XCS-P - 1 个电缆入口
XCS-T - 2 个电缆入口
- II- 操作头
A - 插入型
L - 杠杆型
R - 铰转型
- III- 触头模块
对 XCS-P:
1 - 1NO + 1NC 快动
2 - 2NC 快动
3 - 1NC + 2NO 快动
4 - 2NC + 1NO 快动
5 - 1NO + 1NC 先断后通慢动型
6 - 1NO + 1NC 先通后断慢动型
7 - 2NC 慢动型
8 - 1NC + 2NO 先断后通慢动型
9 - 2NC + 1NO 先断后通慢动型
对 XCS-T:
5 - 1NC + 2NO 先断后通慢动型
7 - 2NC + 1NO 先断后通慢动型
8 - 3NC 慢动型

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 3 页 共 5 页

证书编号: CQC2007010305236411

纸号: 372775

IV -

操纵杆的位置和形式

5-对于铰链型操作头: 转轴长度 30mm

对于杠杆型操作头: 直杠杆中位

6-对于杠杆型操作头: 直杠杆右位或左位

7-对于杠杆型操作头: 折弯杠杆右位

8-对于杠杆型操作头: 折弯杠杆中位

9-对于杠杆型操作头: 折弯杠杆左位

对于插入型操作头: 无闭锁

V -

入口

1-11 号欧洲电缆密封管螺纹孔

2-M16 ISO 电缆密封管螺纹孔

3-1/2 in. NPT 螺纹孔 或提供 1/2 in. NPT 联结头

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 4 页 共 5 页

证书编号: CQC2007010305236411

纸号: 372775

<u>XCS-P</u> I	<u>A</u> II	<u>5</u> III	<u>9</u> IV	<u>1</u> V
-------------------	----------------	-----------------	----------------	---------------

I - Basic Designation of safety limit switch
XCS-P - Isolating, one cable entry
XCS-T - Isolating, two cable entries

II - Operating Head
A - Introducing key
L - Lever
R - Hinge

III - Contact Block
For Models XCS-P:
1 - 1NO + 1NC Snap action
2 - 2NC Snap action
3 - 1NC + 2NO Snap action
4 - 2NC + 1NO Snap action
5 - 1NO + 1NC low action shifted
6 - 1NO + 1NC low action overlapping
7 - 2NC low action simultaneous
8 - 1NC + 2NO Low action shifted
9 - 2NC + 1NO Low action shifted

For Models XCS-T:
5 - 1NC + 2NO low action shifted
7 - 2NC + 1NO low action shifted
8 - 3NC low action simultaneous

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 5 页 共 5 页

证书编号: CQC2007010305236411

纸号: 372775

IV -

Type and position of the operating lever.

5-For hinge operating head: 30mm length of spindle.

For lever operating head: straight lever is centred

6-For lever operating head: straight lever is to right or left

7-For lever operating head: elbowed lever is to right

8-For lever operating head: elbowed lever is centred

9-For lever operating head: elbowed lever is to left

For introducing operating head: without locking of operating key

V -

Entry

1 - Threaded hole(s) for Type 11 European cable gland

2 - Threaded hole(s), M16 type, for ISO cable gland

3 - 1/2 in. NPT threaded hole or provided with one 1/2 in. NPT adaptor.

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>